

## Technical Data Sheet

## EXTASE tinted

<b>Order no.:</b>	277 375	
<b>Product designation:</b>	Safety Spectacle EXTASE tinted	
<b>Applied standard:</b>	DIN EN 166 (DIN = German Institute for Standardization)	
<b>Utilization:</b>	<p>The safety spectacle is ideal for work in the outdoor area with sunlight irradiation. It can be carried in connection with half masks or filtering half masks.</p> <p>The scope of protection is determined by the product information, technical standards and valid application rules.</p>	
<b>Description:</b>	The safety spectacle encloses the eye range.	
<b>Materials:</b>	Frame Nose pad upholstery Temple upholstery Mounting screw Lens	Polycarbonate Polyvinyl chloride Thermoplastic rubber Metal Polycarbonate
<b>Colour of frame:</b>	silver-grey / green	
<b>Lens thickness:</b>	1,3 mm – 2,3 mm	
<b>Lenses colour:</b>	dark grey (reflective)	
<b>Weight:</b>	approx. 33 gram	
<b>Marking:</b>	Trade mark of manufacturer (LOGO) Product designation Applied standard CE-Identification Optical class Operating range Protection level of the eyeglass filters Abbreviation for mechanical firmness	
<b>Marking explanation:</b>	1      Optical class (particularly high requirement of the visual efficiency) 5-3.1    Protection level of the eyeglass filters (ultraviolet protection filter) FT      Mechanical firmness – Impact with low energy at extreme temperatures (-5°C to 55°C)	
<b>Properties:</b>	Anti-Scratch Anti-Fog 99,99% UV-Protection	
<b>Handling:</b>	Take the Safety spectacles from the packing directly before use. Use the Safety spectacles in accordance with the information brochure.	
<b>Storage conditions:</b>	Ambient temperature. Protect against cold, heat and humidity. Consider conditions noted on the information brochure.	
<b>Warning reference:</b>	Please consider the information brochure!	
<b>User references:</b>	EKASTU Safety GmbH guarantees the indicated achievement according to class and type. It is to be noted that the laboratory test values can considerably deviate from those which are reached in practice. This can lead to longer or shorter preservation time. The user must read and understand all functional information. In addition, the knowledge of all relevant application rules absolutely necessary (in particular the application rules according to BGR 192 (use of ocular protection and facial protection)).	