# EKASTU | Safety WIR PRODUZIEREN SICHERHEIT!

## **Technical Data Sheet**

## C 607/Silicone



Order no.: 466 617

#### **Product designation:**

Full Face Mask C 607/Silicone (Class 2)

In connection with respiratory filter (standard thread DIN EN 148-1) as filtering device, in connection with powered filtering device as filtering device, in connection with compressed air line device as breathing apparatus and in connection with unassisted fresh air hose breathing device as breathing apparatus. The scope of protection is determines by the product information, technical standards and valid application rules.



## DESCRIPTION

- · Compact full face mask, fitting any face conformations
- · Polycarbonate visor with high impact resistance to acids, even at high concentrations
- Excellent voice transmission thanks to the frontal position of the speech diaphragm, which allows the use of megaphones, telephones and two-way radios
- Quick donning and doffing; the shoulder strap allows to keep the mask ready for immediate use
- · Easy maintenance, washing and disinfection. All components can be disassembled without special tools

## **MAIN FEATURES**



### **PERFORMANCES**











## I APPLICATION FIELDS









Hospital



Chemical Pharmaceutical Industry



### MATERIALS

- · Face seal: Silicone
- Inner half mask: Ethylene-Propylene-Diene-Mixture (EPDM)
- Disk-Frame: Polyphenylene oxide (PPO)
- Harness: Ethylene-Propylene-Diene-Mixture (EPDM)
- Visor: Polycarbonate (PC)
- Check valve: Rubber
- · Inhalation valve: Rubber
- Exhalation valve: Rubber
- Exhalation valve cap: Polyphenylene oxide (PPO)
- Connector: Polyamide (PA)
- Connector-Clip: Metal
- · Speech diaphragm: Metal

#### MARKING

- Trade mark of manufacturer (LOGO)
- Product designation
- Applied standard
- Manufacture year and -month
- CE-Identification
- Notified body
- Type identifying marking

## **DONNING AND USING**

- · Take the Full face mask from the Packing and/or Storage container directly before use
- · Use the Full face mask in accordance with the information brochure

### STORAGE

- · Ambient temperature. Protect against cold, heat and humidity
- · Consider conditions noted on the packaging

### CERTIFICATIONS

- · The mask is certified as class 2 according to EN 136
- · For use with particle, gas and combined filters equipped with EN 148/1 threaded connection
- Certified according to European Regulation (EU) 2016/425

## **USER REFERENCES**

EKASTU Safety GmbH guarantees the indicated achievement according to class and type. It is to be noted that the laboratory test values can considerably deviate from those, which are reached in practice. The user must read and understand all functional information. Use the Respiratory protective devices with this information brochure, the relevant valid statutory regulations and the safety requirements of the profession associations, particularly the regulations for use in accordance with DGUV Rule 112-190 resp. DIN EN 529 "Respiratory protective devices – recommendation for selection, use, care and maintenance – guidelines".

TD 466617 English\_06-01.24

EKASTU Safety GmbH Schänzle 8 • D-71332 Waiblingen Germany Tel.: +49(0)7151 975099-0 Fax: +49(0)7151 975099-30 Internet: www.ekastu.de eMail: info@ekastu.de

## WEIGHT

• approx. 580 g