

### Technical Data Sheet

### EWB-with funnel, (for 600 ml) EY

|                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|---------------------------------|---------|----------------------------------|------|---------------------------------|-------------------|------------------|----------------|--------------------|----------------------|------------------------------------|
| <b>Order no.:</b>           | 377 951                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Product designation:</b> | EKASTU-Eye Wash Bottle with funnel, (for 600 ml) EY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Applied standard:</b>    | DIN EN 15154-4 (DIN = German Institute for Standardization)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Utilization:</b>         | The first seconds after an accident, where the eyes are exposed to dangerous substances, are decisive in keeping the injury to a minimum. Non plumbed-in eye wash units (eye wash bottles) are designed and intended to be kept in direct proximity to those people working in potentially dangerous areas. The principal duty of these items of equipment is providing first aid.                                                                                                                                                          |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Description:</b>         | The EKASTU-Eye Wash Bottles/-Mountings are manufactured according to DIN EN 15154-4.                                                                                                                                                                                                                                                                                                                                                                                                                                                        |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Materials:</b>           | <p>The materials used are particularly kind of the skin and therefore have no negative effect on human health.</p> <table><tr><td>Bottle:</td><td>Low-density polyethylene (LDPE)</td></tr><tr><td>Funnel:</td><td>High-density polyethylene (HDPE)</td></tr><tr><td>Cap:</td><td>Low-density polyethylene (LDPE)</td></tr><tr><td>Connecting piece:</td><td>Polystyrene (PS)</td></tr><tr><td>tilting valve:</td><td>Polypropylene (PP)</td></tr><tr><td>Tubes 10/13 and 6/8:</td><td>Polyvinyl chloride soft (PVC-Soft)</td></tr></table> | Bottle: | Low-density polyethylene (LDPE) | Funnel: | High-density polyethylene (HDPE) | Cap: | Low-density polyethylene (LDPE) | Connecting piece: | Polystyrene (PS) | tilting valve: | Polypropylene (PP) | Tubes 10/13 and 6/8: | Polyvinyl chloride soft (PVC-Soft) |
| Bottle:                     | Low-density polyethylene (LDPE)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| Funnel:                     | High-density polyethylene (HDPE)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| Cap:                        | Low-density polyethylene (LDPE)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| Connecting piece:           | Polystyrene (PS)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| tilting valve:              | Polypropylene (PP)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| Tubes 10/13 and 6/8:        | Polyvinyl chloride soft (PVC-Soft)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Weight:</b>              | approx. 106 g                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Marking:</b>             | Trade mark of manufacturer (LOGO)<br>Product designation<br>Applied standard<br>Consider the information brochure<br>CE-Identification<br>Storage conditions                                                                                                                                                                                                                                                                                                                                                                                |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Handling:</b>            | Take the Eye Wash Bottle from the packing and/or storage container directly before use.                                                                                                                                                                                                                                                                                                                                                                                                                                                     |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Storage conditions:</b>  | Ambient temperature. Protect against cold, heat and humidity. Consider conditions noted on the packaging. The Eye Wash Bottle shall be subjected by visual inspection at regular intervals.                                                                                                                                                                                                                                                                                                                                                 |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>Warning reference:</b>   | Please consider the information brochure!                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |
| <b>User references:</b>     | EKASTU Safety GmbH guarantees the indicated achievement according to class and type. It is to be noted that the laboratory test values can considerably deviate from those, which are reached in practice. The user must read and understand all functional information. Use the Eye Wash Bottle with this information brochure, the relevant valid statutory regulations and the safety requirements of the profession associations for example DGUV Information 204-022 'First Aid in Operation'.                                         |         |                                 |         |                                  |      |                                 |                   |                  |                |                    |                      |                                    |